


**DETERMINATION OF
CONSISTENCY****CEMENT****AUTOMATIC VICAT APPARATUS (C-090/A/EN)
EN 196-3**

- The reaction between cement and water is the primary cause of the setting of concrete. The setting time for cement and concrete is determined using the Vicat Apparatus.
- By measuring the setting time for concrete/cement via the penetration resistance method (Vicat Apparatus), the time the concrete/cement can stay fresh can be determined. This time indicates the period the mix can stay in the mixer before pouring it into the moulds/frameworks.
- Designed to be fully automatic with very precise and reputable result.
- Test results can be easily printed on any incorporated printer.
- Guiding menu is available in multi-languages (English, French, German and Italian).
- Equipped with a large LCD display to show the test results data. The test will automatically print a report with all data.

**SUPPLIED WITH**

- Movable rod (300 g)
- Vicat Mould (Ø 70 / Ø 80 mm x 40 mm)
- Needle (Ø 1.13 mm)
- Consistency Plunger (Ø 10 mm)
- Container
- Glass Plate

TECHNICAL SPECIFICATIONS

- 220 - 240 V / 50 - 60 Hz